

SB STOCK BREAKERS

STOCK BREAKER PART NUMBER	Description	Included Accessories
SBH5050DVS	BREAKER SB5000 H-RATING DRAWOUT 5000A (no cradle)	
	SB BREAKER 5000A FRAME DRAWOUT VERT BUS 5000 AMP MAX TRIP	SBH5050DV
	STANDARD 5000A SB TRIP UNIT LSI + GF	SB50TLSIG
	5000A RATING PLUG FOR 5000A MAX SB BREAKER RATING	50SB5000
	SECONDARY DISCONNECT - LEFT TOP FOR DRAWOUT SB BREAKER	SBSDLT
	SECONDARY DISCONNECT - LEFT BOTTOM FOR DRAWOUT SB BREAKER	SBSDLB
	SECONDARY DISCONNECT - RIGHT TOP FOR DRAWOUT SB BREAKER	SBSDRT
	SECONDARY DISCONNECT - RIGHT BOTTOM FOR DRAWOUT SB BREAKER	SBSDRB
	120VAC SHUNT TRIP FOR 3200/5000A FRAME SB	SB4ST120
	120VAC MOTOR OPERATOR FOR SB BREAKER	SB4EO120
	AUXILIARY 6A & 6B CONTACTS FOR 3200/5000A FRAME SB BREAKER	SB4AS12
SBH5050FS	BREAKER SB5000 H-RATING FIXED 5000A	
	SB BREAKER 5000A FRAME FIXED BUS 5000 AMP MAX TRIP	SBH5050FS
	STANDARD 5000A SB TRIP UNIT LSI + GF	SB50TLSIG
	5000A RATING PLUG FOR 5000A MAX SB BREAKER RATING	50SB5000
	SECONDARY DISCONNECT - LEFT TOP FOR DRAWOUT SB BREAKER	SBTBLT
	SECONDARY DISCONNECT - LEFT BOTTOM FOR DRAWOUT SB BREAKER	SBTBLB
	SECONDARY DISCONNECT - RIGHT TOP FOR DRAWOUT SB BREAKER	SBTBRT
	SECONDARY DISCONNECT - RIGHT BOTTOM FOR DRAWOUT SB BREAKER	SBTBRB
	120VAC SHUNT TRIP FOR 3200/5000A FRAME SB	SB4ST120
	120VAC MOTOR OPERATOR FOR SB BREAKER	SB4EO120
	AUXILIARY 6A & 6B CONTACTS FOR 3200/5000A FRAME SB BREAKER	SB4AS12
	TERMINAL BLOCK MOUNTS	SBTBM
SBH4040DVS	BREAKER SB4000 H-RATING DRAWOUT 4000A (no cradle)	
	SB BREAKER 4000A FRAME DRAWOUT VERT BUS 4000 AMP MAX TRIP	SBH4040DV
	STANDARD 4000A SB TRIP UNIT LSI + GF	SB40TLSIG
	4000A RATING PLUG FOR 4000A MAX SB BREAKER RATING	40SB4000
	SECONDARY DISCONNECT - LEFT TOP FOR DRAWOUT SB BREAKER	SBSDLT
	SECONDARY DISCONNECT - LEFT BOTTOM FOR DRAWOUT SB BREAKER	SBSDLB
	SECONDARY DISCONNECT - RIGHT TOP FOR DRAWOUT SB BREAKER	SBSDRT
	SECONDARY DISCONNECT - RIGHT BOTTOM FOR DRAWOUT SB BREAKER	SBSDRB
	120VAC SHUNT TRIP FOR 3200/5000A FRAME SB	SB4ST120
	120VAC MOTOR OPERATOR FOR SB BREAKER	SB4EO120
	AUXILIARY 6A & 6B CONTACTS FOR 3200/5000A FRAME SB BREAKER	SB4AS12
SBH4040FS	BREAKER SB4000 H FIXED 4000A	
	SB BREAKER 4000A FRAME FIXED BUS 4000 AMP MAX TRIP	SBH4040F
	STANDARD 4000A SB TRIP UNIT LSI + GF	SB40TLSIG
	4000A RATING PLUG FOR 4000A MAX SB BREAKER RATING	40SB4000
	SECONDARY DISCONNECT - LEFT TOP FOR DRAWOUT SB BREAKER	SBTBLT
	SECONDARY DISCONNECT - LEFT BOTTOM FOR DRAWOUT SB BREAKER	SBTBLB
	SECONDARY DISCONNECT - RIGHT TOP FOR DRAWOUT SB BREAKER	SBTBRT
	SECONDARY DISCONNECT - RIGHT BOTTOM FOR DRAWOUT SB BREAKER	SBTBRB
	120VAC SHUNT TRIP FOR 3200/5000A FRAME SB	SB4ST120
	120VAC MOTOR OPERATOR FOR SB BREAKER	SB4EO120
	AUXILIARY 6A & 6B CONTACTS FOR 3200/5000A FRAME SB BREAKER	SB4AS12
	TERMINAL BLOCK MOUNTS	SBTBM
SBH3232DVS	BREAKER SB3200 H-RATING DRAWOUT 3200A (no cradle)	
	SB BREAKER 3200A FRAME DRAWOUT VERT BUS 3200 AMP MAX TRIP	SBH3232DV
	STANDARD 3200A SB TRIP UNIT LSI + GF	SB32TLSIG
	3200A RATING PLUG FOR 3200A MAX SB BREAKER RATING	32SB3200
	SECONDARY DISCONNECT - LEFT TOP FOR DRAWOUT SB BREAKER	SBSDLT
	SECONDARY DISCONNECT - LEFT BOTTOM FOR DRAWOUT SB BREAKER	SBSDLB
	SECONDARY DISCONNECT - RIGHT TOP FOR DRAWOUT SB BREAKER	SBSDRT
	SECONDARY DISCONNECT - RIGHT BOTTOM FOR DRAWOUT SB BREAKER	SBSDRB
	120VAC SHUNT TRIP FOR 3200/5000A FRAME SB	SB4ST120
	120VAC MOTOR OPERATOR FOR SB BREAKER	SBEO120
	AUXILIARY 6A & 6B CONTACTS FOR 3200/5000A FRAME SB BREAKER	SB4AS12

SB STOCK BREAKERS Cont.

<u>STOCK BREAKER PART NUMBER</u>	<u>Description</u>	<u>Included Accessories</u>
SBH3232FS	BREAKER SB3200 H-RATING FIXED 3200A	
	SB BREAKER 3200A FRAME FIXED BUS 3200 AMP MAX TRIP	SBH3232F
	STANDARD 3200A SB TRIP UNIT LSI + GF	SB32TLSIG
	3200A RATING PLUG FOR 3200A MAX SB BREAKER RATING	32SB3200
	SECONDARY DISCONNECT - LEFT TOP FOR DRAWOUT SB BREAKER	SBTBLT
	SECONDARY DISCONNECT - LEFT BOTTOM FOR DRAWOUT SB BREAKER	SBTBLB
	SECONDARY DISCONNECT - RIGHT TOP FOR DRAWOUT SB BREAKER	SBTBRT
	SECONDARY DISCONNECT - RIGHT BOTTOM FOR DRAWOUT SB BREAKER	SBTBRB
	120VAC SHUNT TRIP FOR 3200/5000A FRAME SB	SB4ST120
	120VAC MOTOR OPERATOR FOR SB BREAKER	SBEO120
	AUXILIARY 6A & 6B CONTACTS FOR 3200/5000A FRAME SB BREAKER	SB4AS12
	TERMINAL BLOCK MOUNTS	SBTBM
SBH3225DVS	BREAKER SB3200 H-RATING DRAWOUT 2500A (no cradle)	
	SB BREAKER 3200A FRAME DRAWOUT VERT BUS 2500 AMP MAX TRIP	SBH3225DV
	STANDARD 2500A SB TRIP UNIT LSI + GF	SB25TLSIG
	3200A RATING PLUG FOR 2500A MAX SB BREAKER RATING	32SB2500
	SECONDARY DISCONNECT - LEFT TOP FOR DRAWOUT SB BREAKER	SBSDLT
	SECONDARY DISCONNECT - LEFT BOTTOM FOR DRAWOUT SB BREAKER	SBSDLB
	SECONDARY DISCONNECT - RIGHT TOP FOR DRAWOUT SB BREAKER	SBSDRT
	SECONDARY DISCONNECT - RIGHT BOTTOM FOR DRAWOUT SB BREAKER	SBSDRB
	120VAC SHUNT TRIP FOR 3200/5000A FRAME SB	SB4ST120
	120VAC MOTOR OPERATOR FOR SB BREAKER	SBEO120
	AUXILIARY 6A & 6B CONTACTS FOR 3200/5000A FRAME SB BREAKER	SB4AS12
SBH3225FS	BREAKER SB3200 H-RATING FIXED 2500A	
	SB BREAKER 3200A FRAME FIXED BUS 2500 AMP MAX TRIP	SBH3225F
	STANDARD 2500A SB TRIP UNIT LSI + GF	SB25TLSIG
	3200A RATING PLUG FOR 2500A MAX SB BREAKER RATING	32SB2500
	SECONDARY DISCONNECT - LEFT TOP FOR DRAWOUT SB BREAKER	SBTBLT
	SECONDARY DISCONNECT - LEFT BOTTOM FOR DRAWOUT SB BREAKER	SBTBLB
	SECONDARY DISCONNECT - RIGHT TOP FOR DRAWOUT SB BREAKER	SBTBRT
	SECONDARY DISCONNECT - RIGHT BOTTOM FOR DRAWOUT SB BREAKER	SBTBRB
	120VAC SHUNT TRIP FOR 3200/5000A FRAME SB	SB4ST120
	120VAC MOTOR OPERATOR FOR SB BREAKER	SBEO120
	AUXILIARY 6A & 6B CONTACTS FOR 3200/5000A FRAME SB BREAKER	SB4AS12
	TERMINAL BLOCK MOUNTS	SBTBM
SBH2020DVS	BREAKER SB2000 H-RATING DRAWOUT 2000A (no cradle)	
	SB BREAKER 2000A FRAME DRAWOUT VERT BUS 2000 AMP MAX TRIP	SBH2020DV
	STANDARD 2000A SB TRIP UNIT LSI + GF	SB20TLSIG
	2000A RATING PLUG FOR 2000A MAX SB BREAKER RATING	20SB2000
	SECONDARY DISCONNECT - LEFT TOP FOR DRAWOUT SB BREAKER	SBSDLT
	SECONDARY DISCONNECT - LEFT BOTTOM FOR DRAWOUT SB BREAKER	SBSDLB
	SECONDARY DISCONNECT - RIGHT TOP FOR DRAWOUT SB BREAKER	SBSDRT
	SECONDARY DISCONNECT - RIGHT BOTTOM FOR DRAWOUT SB BREAKER	SBSDRB
	120VAC SHUNT TRIP FOR 2000A FRAME SB	SBST120
	120VAC MOTOR OPERATOR FOR SB BREAKER	SBEO120
	AUXILIARY 6A & 6B CONTACTS FOR 2000A FRAME SB BREAKER	SBAS12
SBH2020FS	BREAKER SB2000 H-RATING FIXED 2000A	
	SB BREAKER 2000A FRAME FIXED BUS 2000 AMP MAX TRIP	SBH2020F
	STANDARD 2000A SB TRIP UNIT LSI + GF	SB20TLSIG
	2000A RATING PLUG FOR 2000A MAX SB BREAKER RATING	20SB2000
	SECONDARY DISCONNECT - LEFT TOP FOR DRAWOUT SB BREAKER	SBTBLT
	SECONDARY DISCONNECT - LEFT BOTTOM FOR DRAWOUT SB BREAKER	SBTBLB
	SECONDARY DISCONNECT - RIGHT TOP FOR DRAWOUT SB BREAKER	SBTBRT
	SECONDARY DISCONNECT - RIGHT BOTTOM FOR DRAWOUT SB BREAKER	SBTBRB
	120VAC SHUNT TRIP FOR 2000A FRAME SB	SBST120
	120VAC MOTOR OPERATOR FOR SB BREAKER	SBEO120
	AUXILIARY 6A & 6B CONTACTS FOR 2000A FRAME SB BREAKER	SBAS12
	TERMINAL BLOCK MOUNTS	SBTBM

SB BREAKERS Cont.

<u>STOCK BREAKER PART NUMBER</u>	<u>Description</u>	<u>Included Accessories</u>
SBH2016DVS	BREAKER SB2000 H-RATING DRAWOUT 1600A (no cradle)	
	SB BREAKER 2000A FRAME DRAWOUT VERT BUS 1600 AMP MAX TRIP	SBH2016DV
	STANDARD 1600A SB TRIP UNIT LSI + GF	SB16TLSIG
	1600A RATING PLUG FOR 1600A MAX SB BREAKER RATING	16SB1600
	SECONDARY DISCONNECT - LEFT TOP FOR DRAWOUT SB BREAKER	SBSDLT
	SECONDARY DISCONNECT - LEFT BOTTOM FOR DRAWOUT SB BREAKER	SBSDLB
	SECONDARY DISCONNECT - RIGHT TOP FOR DRAWOUT SB BREAKER	SBSDRT
	SECONDARY DISCONNECT - RIGHT BOTTOM FOR DRAWOUT SB BREAKER	SBSDRB
	120VAC SHUNT TRIP FOR 2000A FRAME SB	SBST120
	120VAC MOTOR OPERATOR FOR SB BREAKER	SBEO120
	AUXILIARY 6A & 6B CONTACTS FOR 2000A FRAME SB BREAKER	SBAS12
SBH2016FS	BREAKER SB2000 H-RATING FIXED 1600A	
	SB BREAKER 2000A FRAME FIXED BUS 1600 AMP MAX TRIP	SBH2016F
	STANDARD 1600A SB TRIP UNIT LSI + GF	SB16TLSIG
	1600A RATING PLUG FOR 1600A MAX SB BREAKER RATING	16SB1600
	SECONDARY DISCONNECT - LEFT TOP FOR DRAWOUT SB BREAKER	SBTBLT
	SECONDARY DISCONNECT - LEFT BOTTOM FOR DRAWOUT SB BREAKER	SBTBLB
	SECONDARY DISCONNECT - RIGHT TOP FOR DRAWOUT SB BREAKER	SBTBRT
	SECONDARY DISCONNECT - RIGHT BOTTOM FOR DRAWOUT SB BREAKER	SBTBRB
	120VAC SHUNT TRIP FOR 2000A FRAME SB	SBST120
	120VAC MOTOR OPERATOR FOR SB BREAKER	SBEO120
	AUXILIARY 6A & 6B CONTACTS FOR 2000A FRAME SB BREAKER	SBAS12
	TERMINAL BLOCK MOUNTS	SBTBM
SBH2012DVS	BREAKER SB2000 H-RATING DRAWOUT 1200A (no cradle)	
	SB BREAKER 2000A FRAME DRAWOUT VERT BUS 1200 AMP MAX TRIP	SBH2012DV
	STANDARD 1200A SB TRIP UNIT LSI + GF	SB12TLSIG
	1200A RATING PLUG FOR 1200A MAX SB BREAKER RATING	12SB1200
	SECONDARY DISCONNECT - LEFT TOP FOR DRAWOUT SB BREAKER	SBSDLT
	SECONDARY DISCONNECT - LEFT BOTTOM FOR DRAWOUT SB BREAKER	SBSDLB
	SECONDARY DISCONNECT - RIGHT TOP FOR DRAWOUT SB BREAKER	SBSDRT
	SECONDARY DISCONNECT - RIGHT BOTTOM FOR DRAWOUT SB BREAKER	SBSDRB
	120VAC SHUNT TRIP FOR 2000A FRAME SB	SBST120
	120VAC MOTOR OPERATOR FOR SB BREAKER	SBEO120
	AUXILIARY 6A & 6B CONTACTS FOR 2000A FRAME SB BREAKER	SBAS12
SBH2012FS	BREAKER SB2000 H-RATING FIXED 1200A	
	SB BREAKER 2000A FRAME FIXED BUS 1200 AMP MAX TRIP	SBH2012F
	STANDARD 1200A SB TRIP UNIT LSI + GF	SB12TLSIG
	1200A RATING PLUG FOR 1200A MAX SB BREAKER RATING	12SB1200
	SECONDARY DISCONNECT - LEFT TOP FOR DRAWOUT SB BREAKER	SBTBLT
	SECONDARY DISCONNECT - LEFT BOTTOM FOR DRAWOUT SB BREAKER	SBTBLB
	SECONDARY DISCONNECT - RIGHT TOP FOR DRAWOUT SB BREAKER	SBTBRT
	SECONDARY DISCONNECT - RIGHT BOTTOM FOR DRAWOUT SB BREAKER	SBTBRB
	120VAC SHUNT TRIP FOR 2000A FRAME SB	SBST120
	120VAC MOTOR OPERATOR FOR SB BREAKER	SBEO120
	AUXILIARY 6A & 6B CONTACTS FOR 2000A FRAME SB BREAKER	SBAS12
	TERMINAL BLOCK MOUNTS	SBTBM
SBH2008DVS	BREAKER SB2000 H-RATING DRAWOUT 800A (no cradle)	
	SB BREAKER 2000A FRAME DRAWOUT VERT BUS 800 AMP MAX TRIP	SBH2008DV
	STANDARD 800A SB TRIP UNIT LSI + GF	SB08TLSIG
	800A RATING PLUG FOR 800A MAX SB BREAKER RATING	08SB800
	SECONDARY DISCONNECT - LEFT TOP FOR DRAWOUT SB BREAKER	SBSDLT
	SECONDARY DISCONNECT - LEFT BOTTOM FOR DRAWOUT SB BREAKER	SBSDLB
	SECONDARY DISCONNECT - RIGHT TOP FOR DRAWOUT SB BREAKER	SBSDRT
	SECONDARY DISCONNECT - RIGHT BOTTOM FOR DRAWOUT SB BREAKER	SBSDRB
	120VAC SHUNT TRIP FOR 2000A FRAME SB	SBST120
	120VAC MOTOR OPERATOR FOR SB BREAKER	SBEO120
	AUXILIARY 6A & 6B CONTACTS FOR 2000A FRAME SB BREAKER	SBAS12

SB STOCK BREAKERS Cont.

<u>STOCK BREAKER PART NUMBER</u>	<u>Description</u>	<u>Included Accessories</u>
SBH2008FS	BREAKER SB2000 H-RATING FIXED 800A	
	<i>SB BREAKER 2000A FRAME FIXED BUS 800 AMP MAX TRIP</i>	<i>SBH2008F</i>
	<i>STANDARD 800A SB TRIP UNIT LSI + GF</i>	<i>SB08TLSIG</i>
	<i>800A RATING PLUG FOR 800A MAX SB BREAKER RATING</i>	<i>08SB800</i>
	<i>SECONDARY DISCONNECT - LEFT TOP FOR DRAWOUT SB BREAKER</i>	<i>SBTBLT</i>
	<i>SECONDARY DISCONNECT - LEFT BOTTOM FOR DRAWOUT SB BREAKER</i>	<i>SBTBLB</i>
	<i>SECONDARY DISCONNECT - RIGHT TOP FOR DRAWOUT SB BREAKER</i>	<i>SBTBRT</i>
	<i>SECONDARY DISCONNECT - RIGHT BOTTOM FOR DRAWOUT SB BREAKER</i>	<i>SBTB RB</i>
	<i>120VAC SHUNT TRIP FOR 2000A FRAME SB</i>	<i>SBST120</i>
	<i>120VAC MOTOR OPERATOR FOR SB BREAKER</i>	<i>SBEO120</i>
	<i>AUXILIARY 6A & 6B CONTACTS FOR 2000A FRAME SB BREAKER</i>	<i>SBAS12</i>
	<i>TERMINAL BLOCK MOUNTS</i>	<i>SBTBM</i>

Available Accessories

PART #	DESCRIPTION
04SB400	RATING PLUG-400A RAT W/40
08SB400	RATING PLUG-800A RAT W/40
08SB600	RATING PLUG-800A RAT W/60
08SB800	RATING PLUG-800A RAT W/80
12SB1200	RATING PLUG-1200A RAT W/
12SB600	RATING PLUG-1200A RAT W/6
12SB800	RATING PLUG-1200A RAT W/8
16SB1200	RATING PLUG-1600A RAT W/1
16SB1600	RATING PLUG-1600A RAT W/1
16SB800	RATING PLUG-1600A RAT W/8
20SB1200	RATING PLUG-2000A RAT W/1
20SB1600	RATING PLUG-2000A RAT W/1
20SB2000	RATING PLUG-2000A RAT W/2
25SB2500	2500A RATING PLUG ASS'Y
32SB1600	1600A RATING PLUG ASS'Y
32SB2500	2500A RATING PLUG ASS'Y
32SB3200	3200A RATING PLUG ASS'Y
40SB2000	RATING PLUG-2000A FOR 4K
40SB3000	RATING PLUG-3000A FOR 4K
40SB4000	RATING PLUG-4000A FOR 4K
4CEL4	CELL SWITCH 4 NO 4NC 4000
50SB3000	RATING PLUG-3000A
50SB4000	RATING PLUG-4000A
50SB5000	RATING PLUG -5000A
CEL4	CELL SWITCH

PART #	DESCRIPTION
EP5B4DMK	EXPANSION PLUG (3200, 4000, 5000A) D.O.
EP5B4FMK	EXPANSION PLUG (3200, 4000, 5000A) FIXED
EP5BDMK	EXPANSION PLUG (800, 1200, 2000A) D.O.
EP5BFMK	EXPANSION PLUG (800, 1200, 2000A) FIXED
KISB	KIRK KEY INTERLOCK KITS
N08SB	NEUTRAL SENSOR - 800A
N12SB	NEUTRAL SENSOR SB 1200A
N16SB	NEUTRAL SENSOR SB 1600A
N20SB	NEUTRAL SENSOR SB 2000A
N25SB	NEUTRAL SENSOR SB 2500A
N32SB	NEUTRAL SENSOR SB 3200A
N40SB	NEUTRAL SENSOR SB 4000A
N50SB	NEUTRAL SENSOR SB 5000A
SB12TCON	T-CONNECTOR
SB20TCON	T-CONNECTOR
SB32TCON	T-CONNECTOR
SB40TCON	T-CONNECTOR
SB4AS12	AUX SWITCH ICCB 4KA FRAME
SB4AS4	AUX SWITCH ICCB 4KA FRAME
SB4AS8	AUX SWITCH ICCB 4KA FRAME
SB4ECAKT	RETROFIT WIRING (E-COM)(5000A)
SB4EO120CCX	ELEC. OPER. CLS INTLK 120AC
SB4RCS120	REMOTE CLS SLND 4K-120VAC
SB4RCS125	REMOTE CLS SLND 4K-125VDC
SB4RCS24	REMOTE CLS SLND 4K-24VDC
SB4RCS48	REMOTE CLS SLND 4K-48VDC
SB4ST120	SHUNT TRIP 120VAC ICCB (LARGE FRAME)
SB4UV120	U.V.R. - 120VAC - 3200-4K
SB4UV125	U.V.R. - 125VDC - 3200-4K
SB4UV24	U.V.R. - 24VDC - 3200-4K
SB4UV240	U.V.R. - 240VAC - 3200-4K
SB4UV48	U.V.R. - 48VDC - 3200-4K
SB4UV480	U.V.R. - 480VAC - 3200-4K
SB4UV600	U.V.R. - 600VAC - 3200-4K
SB50TCON	T-CONNECTOR
SBAS12	AUXILIARY SWITCH 6NO/6NC
SBAS2	AUXILIARY SWITCH 1NO/1NC
SBAS4	AUXILLARY SWITCH 2NO/2NC
SBAS8	AULILIARY SWITCH 4NO/4NC
SBBA120	BELL ALRM/DIS MOD RLY 120
SBBA24	BELL ALRM/DIS MOD RLY 24V
SBDM	DISPLAY MODULE ICCB
SBECAKT	RETROFIT WIRING (E-COM)(800-3200A)
SBECBA120	EC BELL ALARM/REMOTE OPEN
SBECBA24	EC REMOTE OPEN/CLOSE BA
SBECDMR120	EC DISPLAY MODULE RELAY/
SBE0120	ELECTRIC OPERATOR, 120VAC
SBE0120CCX	ELECTRIC OPERATOR 120VAC
SBE024CCX	ELECTRIC OPERATOR 24DC
SBEPS	EXTERNAL POWER SUPPLY
SBGFM	GRND FAULT MONITOR ASS'Y
SBLD	LIFTING DEVICE SB2000 D/O
SBLD4	LIFTING DEVICE SB 4000A
SBPTM240	240 VRMS PT MODULE
SBPTM480	480 VRMS PT MODULE
SBPTM600	600 VRMS PT MODULE
SBRCS120	REMOTE CLOSE SLNID-120VAC
SBRCS125	REMOTE CLOSE SLNID-125VDC
SBRCS24	REMOTE CLOSE SLNOID 24VDC
SBRCS48	REMOTE CLOSE SLNOID 48VDC

PART #	DESCRIPTION
SBSDLB	SEC. DISCONNECT L BOTTOM
SBSDLT	SEC. DISCONNECT L.TOP
SBSDRB	SEC. DISCONNECT R. BOTTOM
SBSDRT	SEC. DISCONNECT R. TOP
SBSS08	DRAWOUT SAFETY SHUTTERS
SBSS20	DRAWOUT SAFETY SHUTTERS
SBSS32	SHUTTER ASSY 3200A ICCB
SBSS40	SHUTTER ASS'Y 4000A ICCB
SBST120	SHUNT TRIP 120VAC ICCB
SBST240	SHUNT TRIP 240 VAC ICCB
SBST480	SHUNT TRIP 480 VAC ICCB
SBTBLB	TERMINAL BLOCK-LFT BOTTOM
SBTBLT	TERMINAL BLOCK-LEFT TOP
SBTBM	TERMINAL BLOCK MOUNT
SBTBRB	TERMINAL BLOCK RT. BOTTOM
SBTBRT	TERMINAL BLOCK-RIGHT TOP
SBUV120	UNDERVOLTAGE RELESE 120AC
SBUV125	UNDERVOLTAGE RELESE 125DC
SBUV24	UNDERVOLTAGE RELEASE 24DC
SBUV240	UNDERVOLTGE RELESE 240AC
SBUV48	UNDERVOLTAGE RELEASE 48DC
SBUV480	UNDERVOLTGE RELESE 480VAC
SBUV600	UNDERVOLTAGE RELESE 600AC
SISB	SUPERIOR KEY INTERLOCK KITS
SBH20DFV	SB2000 STATIONARY D/O
SBH32DFV	SB3200A STATIONARY D/O
SBH40DFV	STATIONARY DRAWOUT-4000A
SBH50DFV	STATIONARY DRAWOUT-5000A
SBS08DFV	STATIONARY DRAWOUT-800 V
SBS12DFV	STAT. DRAWOUT
SB04TLSIG	T.U.-400A RAT-LT, ST, INS
SB08TLSIG	T.U.-800A RAT-LT, ST, INS
SB08TP02G	EC TU-800 AMP PREMIUM W/
SB12TLSIG	T.U-1200A RAT-LT, ST, INS
SB12TP02G	EC TU-1200 AMP PREMIUM W/
SB16TLSIG	T.U.-1600A RAT-LT, ST, IN
SB16TP02G	EC TU-1600 AMP PREMIUM W/
SB20TLSIG	T.U.-2KA RAT-LT,ST,IN,GF
SB20TP02G	EC TU-2000 AMP PREMIUM W/
SB25TLSIG	ICCB TRIP UNIT FINAL ASSY
SB25TP02G	EC TU-2500 AMP PREMIUM W/
SB32TLSIG	ICCB TRIP UNIT FINAL ASSY
SB32TP02G	EC TU-3200 AMP PREMIUM W/
SB40TLSIG	T.U.-4000A-LT,ST,INS & GF
SB50TLSIG	TRIP UNIT-5000A
SB50TP02G	EC TU-5000 AMP PREMIUM W/